

Multi Lock Adaptor MLA 6P
 Art. 910.51.088

Lieferumfang
 Scope of delivery
 Contenu de la fourniture
 Dotazione di forniture
 Volumen de envío

Stromversorgungskabel
 Power supply cable
 Câble d'alimentation
 Cavo alimentazione
 Cable alimentación
 l= 50 cm

DFT Kabel
 DFT Cable
 Câble DFT
 Cavo DFT
 Cable DFT
 l= 50 cm




MLA 6P

Maße, Anschlüsse
 Dimensions, connections
 Dimensions, connexions
 Misure, connessioni
 Medidas, conexiones

Schrauben
 Screws
 Vis
 Viti
 Tornillos

HOSPA 4 x 35 / 4 x 55

MLA 6P und Kabel sind im Möbel zu befestigen!
 MLA 6P and cables have to be fastened to the furniture!
 MLA 6P et le cables doivent être fixé dans le meuble!
 MLA 6P e i cavi debbano essere avitato nel mobile!
 Hay que monta el MLA 6P y los cables en el mueble!




Technische Daten / Technical data / Specifications techniques / Dimensions, connections / Dati tecnici / Datos técnicos

Stecker Stromversorgung / Connector power supply / Prise d'alimentation / Spina d'alimentazione / Enchufe para alimentación	AMP Mate-N-Lock
Buchse EFL / Output jack EFL / Prise femelle EFL / Bussola EFL / Casquillo EFL	RJ 10
Buchse DFT / Input jack DFT / Prise femelle DFT / Bussola DFT / Casquillo DFT	Molex 87833-042
Kontakt NC / Contact NC / Contact NC / Contatto NC / Contacto NC	24 V, 1A max.
Temp. Bereich / Temp. Range / Gamme de température / Campo di temperatura / Ámbito de temperatura	0 – 50 °C




Einsatz nur im Innenbereich / For interior use only / Seulement dans domaines internes / Solo per l'uso dentro
 Solo per el empleo en zonas interiores

Anschluss EFL 3/3C und DFT V2
 Connecting EFL 3/3C and DFT V2
 Connecter EFL 3/3C et DFT V2
 Connettere EFL 3/3C e DFT V2
 Conectar EFL 3/3C y DFT V2




EFL-3 Überwachungskontakte werden zum DFT durchgeschaltet.
 EFL 3 monitoring contacts are connected to DFT
 Les contacts de supervision des EFL 3 sont connectés au DFT
 I contatti di monitoraggio delle EFL 3 sono connessi al DFT
 Contactos de supervisión del los EFL 3 están conectados al DFT

Schaltkontakt, ext.
 Monitoring contact, ext.
 Contact de supervision, ext.
 Contatto di monitoraggio, ext.
 Contacto de supervisión, ext.



Steckerausrichtung am MLA 6P beachten!
 Observe MLA 6P connector orientation
 Observe l'orientation du connecteur MLA 6P
 Osservi l'orientamento della spina MLA 6P
 Atende en orientacion de enchufe MLA 6P



Zubehör / Accessories / Accessoires / Accessori / Accesorios

①	l=	Art.Nr.
Kabel Cable Câble Cavo Cable	0,5m	237.56.340
	1m	237.56.341
	3m	237.56.343
	5m	237.56.345

②	l=	Art.Nr.
Kabel Cable Câble Cavo Cable	1m	823.28.318
	2m	823.28.327
	5m	823.28.350
	10m	823.28.360